

# Model ED 115 | Drying and heating chambers Avantgarde.Line with natural convection

## BENEFITS

- Excellent temporal and spatial temperature accuracy
- High energy efficiency
- USB connection for recording data
- Temperature range up to 300 °C



## MAIN FEATURES

- Temperature range: ambient temperature plus 6 °C to 300 °C
- High temperature accuracy thanks to APT.line™ technology
- Natural convection
- Controller with LCD display
- Electromechanical control of the exhaust air flap
- 2 chrome-plated racks
- Stackable
- Class 2 independent temperature safety device (DIN 12880) with visual temperature alarm
- Ergonomic handle design
- USB port for recording data

## ORDERING INFORMATION

| Interior volume [L] | Voltage           | Option model | Version      | Art.-No.  |
|---------------------|-------------------|--------------|--------------|-----------|
| Model ED 115        |                   |              |              |           |
| 114                 | 230 V 1~ 50/60 Hz | Standard     | ED115-230V   | 9010-0335 |
|                     | 120 V 1~ 60 Hz    | Standard     | ED115UL-120V | 9010-0336 |

## TECHNICAL DATA

| Description  | ED115-230V | ED115UL-120V |
|--|------------|--------------|
| Article Number   | 9010-0335  | 9010-0336    |
| Performance Data Temperature                             |            |              |
| Temperature range 6 °C above ambient temperature to [°C] | 300        | 300          |
| Temperature variation at 150 °C [± K]                    | 2.0        | 2.0          |
| Temperature fluctuation at 150 °C [± K]                  | 0.4        | 0.4          |
| Heating-up time to 150 °C [min]                          | 45         | 45           |
| Recovery time after 30 seconds door open at 150 °C [min] | 16         | 16           |

| Description                           | ED115-230V | ED115UL-120V |
|---------------------------------------|------------|--------------|
| Article Number                        | 9010-0335  | 9010-0336    |
| <b>Electrical data</b>                |            |              |
| Rated Voltage [V]                     | 230        | 120          |
| Power frequency [Hz]                  | 50/60      | 60           |
| Nominal power [kW]                    | 1.25       | 1.35         |
| Unit fuse [A]                         | 6.3        | 12.5         |
| Phase (Nominal voltage)               | 1~         | 1~           |
| <b>Measures - Outer dimensions</b>    |            |              |
| Width net [mm]                        | 710        | 710          |
| Height net [mm]                       | 735        | 735          |
| Depth net [mm]                        | 605        | 605          |
| Wall clearance back [mm]              | 160        | 160          |
| Wall clearance sidewise [mm]          | 100        | 100          |
| <b>Measures - Doors</b>               |            |              |
| Unit doors                            | 1          | 1            |
| <b>Measures - Internal Dimensions</b> |            |              |
| Width [mm]                            | 510        | 510          |
| Height [mm]                           | 530        | 530          |
| Depth [mm]                            | 425        | 425          |
| <b>Measures</b>                       |            |              |
| Interior volume [L]                   | 114        | 114          |
| Net weight of the unit (empty) [kg]   | 54         | 54           |
| permitted load [kg]                   | 150        | 150          |
| Load per rack [kg]                    | 30         | 30           |
| <b>Environment-specific data</b>      |            |              |
| Energy consumption at 150 °C          | 250 Wh/h   | 250 Wh/h     |
| <b>Fixtures</b>                       |            |              |
| Number of shelves (standard/maximum)  | 2/5        | 2/5          |

## OPTIONS AND ACCESSORIES

| Designation                    | Description                                    | *      | Art.-No.  |
|--------------------------------|--|--------|-----------|
| Access port with silicone plug | 10 mm, back                                    | 01     | 8012-0390 |
|                                | 10 mm, left                                    | 01     | 8012-0388 |
|                                | 10 mm, right                                   | 01     | 8012-0387 |
|                                | 10 mm, top                                     | 01     | 8012-0386 |
|                                | 30 mm, back                                    | 01     | 8012-0540 |
|                                | 30 mm, left                                    | 01     | 8012-1018 |
|                                | 30 mm, right                                   | 01     | 8012-1017 |
|                                | 30 mm, top                                     | 01     | 8012-0539 |
|                                | 50 mm, back                                    | 01     | 8012-0546 |
|                                | 50 mm, left                                    | 01     | 8012-1022 |
|                                | 50 mm, right                                   | 01     | 8012-1021 |
|                                | 50 mm, top                                     | 01     | 8012-0545 |
|                                | 100 mm, left                                   | 01     | 8012-1030 |
|                                | 100 mm, right                                  | 01     | 8012-1031 |
|                                | 100 mm, top                                    | 01, 10 | 8012-1029 |
| Analog output, 4 – 20 mA       | for temperature values (output not adjustable) | 02     | 8012-0941 |

\* Notes › See last page

| Designation                                     | Description  | *      | Art.-No.  |
|---|--|--------|-----------|
| Calibration certificate, expanded               | each measurement at additional measuring point or testing temperature  | -      | 8012-0022 |
| Calibration certificate, temperature            | for temperature, measurement in center of chamber at specified temperature   | -      | 8012-0030 |
|   | temperature measurement incl. certificate and 27 measuring points at specified temperature                             | -      | 8012-0921 |
|   | temperature measurement incl. certificate, 15- 18 measuring points at specified temperature                            | -      | 8012-0918 |
|   | temperature measurement incl. certificate, 9 measuring points at specified temperature                                 | -      | 8012-0915 |
| Cart  | stable cart, casters with locking brakes   | -      | 9051-0018 |
| Class 3.1 independent temperature safety device | with visual alarm (DIN 12880)  | 04, 12 | 8012-0985 |
| Clock, battery-backed                           | Real-time clock  | -      | 8012-0981 |
| Data Logger Kit                                 | T 350: temperature logging from 0 °C to 350 °C   | 19     | 8012-0714 |
| Data Logger Kit, software                       | LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable) | 19     | 8012-0821 |
| Door gasket                                     | made of FKM, silicone-free   | 03     | 8012-1009 |
| Door lock                                       | lockable door handle   | -      | 8012-1025 |
| Ethernet interface                              | for communication software   | -      | 8012-0986 |
| Instrument tray                                 | large  | -      | 4022-0124 |
|   | small  | -      | 4022-0123 |
| Interior lighting                               | with 1x 15 W (not available in combination with interior socket)   |        |           |
|   | 120 V option model   | -      | 8012-0971 |
|   | 230 V option model   | -      | 8012-0969 |
| Measurement of air exchange rate                | in accordance with ASTM D5374, definition and protocol according to ambient temperature                                | -      | 8012-0195 |
| Overheating alarm                               | audible, can be switched off, adjustable limit on the independent temperature safety device                            | -      | 8012-0979 |
| pH-neutral detergent                            | concentrated, for gentle remove of residual contaminants; 1 kg   | -      | 1002-0016 |
| Pt 100 temperature sensor                       | additional Pt 100, with flexible cable   | -      | 8012-0940 |
| Rack  | chrome plated  | -      | 6004-0175 |
|   | stainless steel  | -      | 6004-0159 |
| Rack, heavy-load                                | stainless steel (1.4301/AISI 304), max. load per rack 70 kg, max. total load 150 kg                                    | -      | 6004-0202 |
| Rubber pads                                     | set of 4 anti-slip feet, for safe stacking of unit   | 10     | 8012-0001 |
| Shelf, perforated                               | stainless steel  | -      | 6004-0191 |
| Software  | APT-COM™ communications software   |        |           |
|   | version 2 to 3, GLP edition  | 19     | 9053-0016 |
|   | version 3, BASIC edition   | 19     | 9053-0014 |
|   | version 3, GLP edition   | 19     | 9053-0015 |
|   | version 3, STANDARD edition  | 19     | 9053-0013 |
| Viewing window and interior lighting            | APT-COM™ communications software, price: for free  |        |           |
|   | version 3, GLP DEMO Edition  | 19     | 9053-0008 |
| Viewing window and interior lighting            | viewing window (triple insulating glass) in door, 370 x 370 mm, and 15 W interior                                      |        |           |
|   | 120 V option model   | -      | 8012-1063 |
|   | 230 V option model   | -      | 8012-1060 |

\* Notes › See last page

## SERVICES

| Designation                  | Description  | *      | Art.-No. |
|------------------------------|--|--------|----------|
| <b>Installation services</b> |  |        |          |
| Installation                 | and set up of unit at operating location, connect to existing connections  | 13, 18 | DL100100 |
| Instruction                  | unit function instructions for operation and programming of the controller | 18     | DL100400 |

\* Notes › See last page

| Designation                                 | Description   | *                 | Art.-No.  |
|---|---|-------------------|-----------|
| <b>Preventive maintenance</b>               |   |                   |           |
| Preventive maintenance                      | Executive of equipment inspection according to maintenance plan   | 14, 18            | DL200200  |
| <b>Calibration services</b>                 |   |                   |           |
| Calibration temperature                     | including certificate, one measuring point in center of chamber at specified temperature  | 14, 16,<br>17, 18 | DL300101  |
| Measurement of air exchange rate            | including certificate (in accordance with ASTM D5374)   | 14, 16,<br>17, 18 | DL330000  |
| Temperature measurement 18 measuring points | including certificate, 18 measuring points at specified temperature   | 14, 16,<br>17, 18 | DL300118  |
| Temperature measurement 27 measuring points | including certificate, 27 measuring points at specified temperature   | 14, 16,<br>17, 18 | DL300127  |
| Temperature measurement 9 measuring points  | including certificate, 9 measuring points at specified temperature  | 14, 16,<br>17, 18 | DL300109  |
| <b>Validation services</b>                  |   |                   |           |
| Execution of IQ/OQ                          | in accordance with qualification folder   | 15, 18,<br>20     | DL400100  |
| Execution of IQ/OQ/PQ                       | in accordance with customer's requirement, price: on request  | 15, 18            | DL440500  |
| Qualification folder IQ/OQ                  | supporting documents for validation performed by customer, consisting of: IQ/OQ checklists, unit schematics, QM certificate in accordance with ISO 9001     | 15, 18,<br>20     | 8012-0761 |
| Qualification folder IQ/OQ/PQ               | supporting documents for validation performed by customer, in accordance with customer's requirement, extension of Qualification folder IQ/OQ by chapter PQ | 15, 18            | 8012-0942 |
| <b>Warranty service</b>                     |   |                   |           |
| Extension of the warranty from 2 to 3 years | beginning with the date of delivery, wearing parts are not included   | -                 | DL002041  |
| Extension of the warranty from 2 to 5 years | beginning with the date of delivery, wearing parts are not included   | -                 | DL002042  |

\* Notes › See last page

## NOTES

- 01 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.
- 03 Heat resistant only to max. 200 °C.
- 04 Only available on units rated for 230 V.
- 06 Heating-up time may increase as a result of the lower heat conductivity.
- 07 The additional heat input may affect the temperature behavior.
- 09 Not in conjunction with the optional access port, door with window and interior lighting.
- 10 Not available on 23-liter units.
- 11 Not available on 23- or 53-liter units.
- 12 Only available on units rated for 230 V or 400 V.
- 13 Installation and connections take place at unit location; transport within the company only upon consultation.
- 14 We recommend a BINDER service contract (see the chapter on BINDER Service) to cover unit inspections, calibrations and validations.
- 15 OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- 16 Sensor calibration is performed in an accredited calibration laboratory.
- 17 Calibration is performed according to the BINDER factory standard.
- 18 Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).
- 19 For additional accessories, refer to the Process documentation chapter.
- 20 When ordering IQ/OQ qualification folders and associated IQ/OQ execution on one order, we offer a 15 % discount for both items.  
When ordering IQ/OQ/PQ qualification folders and associated IQ/OQ/PQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ/PQ folder.
- 21 ATEX conformity:  
Pumping chamber (pumped gases): II 2G IIC T3 X  
Environment with inert purge gas: II 2G IIB T4 X  
Environment without inert purge gas: II 3G IIB T4 X  
Motor: II 2G Ex d IIB T4 Gb

BINDER GmbH  
Tuttlingen, Germany  
TEL +49 7462 2005 0  
FAX +49 7462 2005 100  
info@binder-world.com  
www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.  
Kowloon, Hong Kong, P.R. China  
TEL +852 39070500  
FAX +852 39070507  
asia@binder-world.com  
www.binder-world.com

Representative Office for CIS  
Moscow, Russia  
TEL +7 495 988 15 16  
FAX +7 495 988 15 17  
russia@binder-world.com  
www.binder-world.ru

BINDER Environmental Testing  
Equipment (Shanghai) Co., Ltd.  
Shangha, P.R. China  
TEL +86 21 685 808 25  
FAX +86 21 685 808 29  
china@binder-world.com  
www.binder-world.com

BINDER Inc.  
Bohemia, NY, USA  
TEL +1 631 224 4340  
FAX +1 631 224 4354  
usa@binder-world.com  
www.binder-world.us